

The solenoid valve block 2-row made of 1.4305 is used for stream switching up to 10 different streams. The second valve row is for quick pre purging. These valves are activated shortly before the dedicated stream is analyzed. The valves are rapid switching solenoid valves, which have a very long life time - tested over 500 million switching operations. The connections for the individual sample gases and the calibration gases are made by flange adapters, which have integrated sinter metal filters. In addition the sample gas inlet can be equipped with a continuously bypass. The valve block has a common tubule which is connected to the analyzer. The other side of the tubule has a blind flange. Alternatively at low concentrations this flange will be changed by a capillary for a very low split flow. This solenoid valve block is used in applications for gas filling plants or for applications with very expensive gases where low gas consumption is essential or in applications with a lot sample inputs while at the same time low cycle time is needed.

### **Options**

Number of valves: up to 20 valves

Type of valve: standard; for oxygen application; for moisture analysis

• Electrical connection: soldering lug; cable

• Split flow: yes/no

Bypass: per sample stream


Check valve: per outlet

• Gas connection: double ferrule fittings: 2 mm; 3 mm; 6 mm; 1/16"; 1/8"; 1/4"

hose: 4.3 mm; 6 mm

• Filter: 20 μm; 50 μm

### **Application example**



Tel.: +49 8466 / 9415 - 0

Fax: +49 8466 / 9415 - 49

### **Technical data**

• Flow coefficient K:

#### Valve:

• Type: 2/2 - ways solenoid valve NC

Voltage: 24 VDC
 Power consumption: 1.5 Watt
 Response time: < 10 ms</li>
 Orifice: 1.25 mm

Max. gas pressure:
 7.0 bar for NC; 3.5 bar for NO

Ambient temperature: -20°C to +60°C
 Gas temperature: 0°C to 60°C
 Housing: 1.4016
 Seal material: FKM
 Type of protection: IP40

• Electrical connection: soldering lug or cable tail (length 700 mm)

0.025 m<sup>3</sup>/h

Materials of wetted parts: 1.4016; FKM

Special models: for oxygen application

for moisture analysis

for oxygen application and moisture analysis

#### **Solenoid valve block:**


• Material: 1.4305

• Dimensions (W x H x D): (depending on configuration)

3-fold with solenoid valves and connections =  $130 \times 70 \times 110$  mm 6-fold with solenoid valves and connections =  $210 \times 70 \times 110$  mm

• Gewicht: 3-fold with solenoid valves and connections = ca. 1.25 kg


6-fold with solenoid valves and connections = ca. 2.43 kg




Tel.: +49 8466 / 9415 - 0

Fax: +49 8466 / 9415 - 49

## Configuration standard solenoid valve block



Date:	
Company:	
Name:	



#### **Remarks:**

Anti-surge diode

B:	Blind flange
K2:	Double ferrule fitting 2 mm
K3:	Double ferrule fitting 3 mm
K6:	Double ferrule fitting 6 mm
K16:	Double ferrule fitting 1/16"
K18:	Double ferrule fitting 1/8"
K14:	Double ferrule fitting 1/4"
D 4	11 4.3

R4: Hose 4.3 mm R6: Hose 6 mm

RV: Check valve
WA: Angle adapter
F20: Filter 20 µm
F50: Filter 50 µm

BS: Blind screw S: 2/2-ways

SK: 2/2-ways with cable

STD: Standard valve
H: For moisture analysis
O: For oxygen application
Y: For moisture analysis +
For oxygen application

Tel.: +49 8466 / 9415 - 0

Fax: +49 8466 / 9415 - 49

Adapter board with LED and anti-surge diode



Fillable form at:

www.cgs-company.de/downloads/MDZ\_E\_D\_MVB-2.pdf

# **Spare parts**

Order No.	Article
1026309	Sintered metal frit set (10 pcs.); pore size 50 μm
1026308	Sintered metal frit set (10 pcs.); pore size 20 μm
1026311	O-ring set; flange 24 (10 pcs.); FKM 6.00x2.00 mm
1027879	Flange set; flange 24; 6 mm Tube Fitting
1027882	Flange set; flange 24; 3 mm Tube Fitting
1027885	Flange set; flange 24; 2 mm Tube Fitting
1027881	Flange set; flange 24; 1/4" Tube Fitting
1027883	Flange set; flange 24; 1/8" Tube Fitting
1027886	Flange set; flange 24; 1/16" Tube Fitting
1027898	Flange set; flange 24; Hose 4.3 mm
1027900	Flange set; flange 24; Hose 6 mm
1027902	Blind flange set for flange 24
1010547	Blind screw; instead of screw in solenoid valve
1027694	Solenoid valve; 2-ways; 24 VDC; FKM; with soldering lug
1027695	Solenoid valve; 2-ways; 24 VDC; FKM; with connection cable 700 mm
1024302	Solenoid valve; H2O; 2-ways; 24 VDC; FKM; with soldering lug
1024306	Solenoid valve; H2O; 2-ways; 24 VDC; FKM; with connection cable 700 mm
1030681	Solenoid valve; O2; 2-ways; 24 VDC; FKM; with soldering lug
1030682	Solenoid valve; O2; 2-ways; 24 VDC; FKM; with connection cable 700 mm
1030685	Solenoid valve; O2; 2-ways; 24 VDC; FKM; with soldering lug
1030686	Solenoid valve; O2; 2-ways; 24 VDC; FKM; with connection cable 700 mm
1027696	Solenoid valve; 3/2-ways; 24 VDC; FKM; with soldering lug
1019762	Solenoid valve; 3/2-ways; 24 VDC; with connection cable 300 mm
1024193	Solenoid valve; H2O; 3/2-ways; 24 VDC; with soldering lug
1024308	Solenoid valve; H2O; 3/2-ways; 24 VDC; with connection cable 300 mm
1030683	Solenoid valve; O2; 3/2-ways; 24 VDC; FKM; with soldering lug
1030684	Solenoid valve; O2; 3/2-ways; 24 VDC; with connection cable 300 mm
1030687	Solenoid valve; H2O; O2; 3/2-ways; 24 VDC; FKM; with soldering lug
1030688	Solenoid valve; H2O; O2; 3/2-ways; 24 VDC; with connection cable 300 mm
1030849	O-ring set screw in solenoid valve (2*10 pcs.); FKM 14.00x1.78 mm; FKM 6.60x1.50 mm
1017821	Adapter board; LED module; 24V
1030851	Free-wheeling diode set (10 pcs.) for solenoid valve
1017105	Hook spanner for screw in solenoid valve; DIN 1810
1027187	Socket wrench for screw in solenoid valve
1016639	Check valve

Tel.: +49 8466 / 9415 - 0 Fax: +49 8466 / 9415 - 49